




THE CALCULATED MTF VALUES ARE DISPLAYED BELOW AND ARE VERIFIED AT THE MAXIMUM F/N AND THE BEST FOCUS PLANE.  
THE COLORED LINES REPRESENT THE F.O.V. STARTING FROM THE CENTER (0%) TO THE CORNER (100%).



— Diff. Limit-Tangential	--- Diff. Limit-Sagittal	— 0,0000 mm-Tangential
--- 0,0000 mm-Sagittal	— 4,8720 mm-Tangential	--- 4,8720 mm-Sagittal
— 6,8880 mm-Tangential	--- 6,8880 mm-Sagittal	— 8,4000 mm-Tangential
--- 8,4000 mm-Sagittal		

Polychromatic Diffraction MTF	
06/08/2019 Data for 0,4000 to 1,7000 $\mu\text{m}$ . Surface: Image	Optec S.p.A. Optical & Optoelectronic Systems
Legend items refer to Field positions	prova.3.b.zmx Configuration 1 of 1

MORE DETAILS ARE AVAILABLE UPON REQUEST AND TECHNICAL DRAWINGS ARE OPEN FOR THE CUSTOMERS AND THEIR NEEDS.